

## Dispensers

### Bottletop dispensers, without bottle

- a positive displacement plunger with a PFA seal minimizes the crystallization of liquids and thus the clogging of the plunger
- high-quality materials (ETFE, PFA, FEP, borosilicate glass, platinum-iridium) ensure high chemical resistance against most acids, solvents and bases
- scale easily readable
- quick, easy and precise volume adjustment
- no drops after tube has been capped
- completely autoclavable at 121 °C
- conformity certified acc. to DIN 12 600
- tolerances acc. to DIN EN ISO 8655-5
- individual serial number on each dispenser
- detailed instruction manual and quality certificate attached
- supplied with 3 adapters, 1 intake tube and 1 mounting tool

#### SUPERIOR

Cat. No.	volume range	volume steps	thread	adapters
53 260 28	0,5-2,5 ml	0,05 ml	GL 32	GL 28, 40, 45
53 260 04	1,0-5,0 ml	0,10 ml	GL 32	GL 28, 40, 45
53 260 05	2,0-10,0 ml	0,20 ml	GL 32	GL 28, 40, 45
53 260 06	5,0-25,0 ml	0,50 ml	GL 45	GL 32, 38, S 40
53 260 08	10,0-50,0 ml	1,00 ml	GL 45	GL 32, 38, S 40
53 260 09	20,0-100,0 ml	2,00 ml	GL 45	GL 32, 38, S 40

#### SUPERIOR "HF"

Cat. No.	volume range	volume steps	thread	adapters
53 250 05	1,0-10,0 ml	0,20 ml	GL 45	GL 32, 38, S 40



accessories:

- [Dispenser bottles](#)

Connect With Us

