Stirring Line

AGE

up to 1200 rpm

Technical Data

Electronic speed regulation:

Epoxy painted metal structure studied and tested in order to give to the instrument an excellent resistance to the attack of chemical and mechanical agents and to corrosion in general.

High-power driving magnet type "PCM" operated by a mono-phase motor for continuous operation	

Stirring volume (H2O):	up to 8 liters
Power:	40W
Weight:	1,8 kg (4 lb)

Dimension (WxHxD): 171x75x190 mm (6.7x2.9x7.5 in)

Magnetic stirrer

Magnetic stirrer with electronic speed adjustment up to 1200 rpm by means of a continuous regulator. Suitable for common laboratory stirring requirements.

Instruments	Power supply	Code No
AGE	230 V / 50 Hz	F20320164
AGE	230 V / 60 Hz	F20330164
AGE	115 V / 60 Hz	F20340164
Optional accessories		Code No
Magnetic stir bar 6x35 mm		A00001056
Magnetic stir bar 6x20 mm		A00001057
annual and a second second		

A00001056 A00001057







