



Nuova™ Porcelain Top



Nuova Stirrer

Includes FREE Stirbar

Product Description

- Die cast aluminum case provides durability.
- Porcelain-coated stainless steel top gives excellent corrosion resistance.
- Topside drip edge protects internal components in case of spillage.
- All units include an integral ring stand holder to accommodate a 0.5" (1.3 cm) diameter support rod.
- Accommodates up to 20 lb. (9.1 kg) loads
- Excellent slow speed stirring (100 rpm) achieved by turning control knob to speed setting "1."

Great Full-Range Stirring!

- Low profile
- Excellent low speed stirring
- Porcelain coated top plate for chemical resistance



Applications

- General lab mixing
- Titrations stirring
- Preparing culture media
- Slow speed stirring of culture media

PRODUCT SPECIFICATIONS

Type	Top Plate Dimensions Inches (cm)		Overall Dimensions Inches (cm)		
	W	D	W	H	D
S18500	7 (17.7)	7 (17.7)	11.8 (29.9)	4.5 (11.43)	8.6 (21.8)

ORDERING INFORMATION

Model #	Volts	Electrical (50/60 Hz) Amps	Watts	Stirring Speed Range (rpm)	Shipping Weight Lb. (kg)
S18525 ^{1,2}	120	0.3	18	100-1000	10 (4.5)
S18520 ²	240	0.1	11	100-1000	10 (4.5)
S18520-26	240	0.1	11	100-1000	10 (4.5)

¹ UL, ² CUL

-26 Models supplied with European cord set.